

PROTEIN CRYSTAL GROWTH CHAMBERS

Protein crystals have been grown in our chambers for over 20 years. The uniform temperature and low vibration environment these models provide allows for optimum crystalline development.

Ten lipped stainless steel trays per door offer 38 or 75 ft² of shelf space, with horizontal air flow across each tray. Microprocessor temperature control combined with horizontal air flow maintains uniformity to $\pm 1^{\circ}\text{C}$ of setpoint. A hi/low alarm monitors chamber temperature and electronic failsafes shut it down to preserve temperature in the rare event of a temperature excursion. These models sit on vibration absorbing pads to isolate them from floor vibrations, and metal to metal contact inside the chamber is also dampened. Options such as a chart recorder, RS-232 or re-transmits for computer monitoring and recording, solid doors, access ports, lockable Plexiglas[®] control cover, etc. are available.



- Microprocessor controlled 5-40°C temperature range, $\pm 0.5^{\circ}\text{C}$ at the sensor
- Audible/Visual Temperature Alarm with relay and electronic failsafe setpoints
- Stainless steel interior with gray powder coat steel exterior
- Ten stainless steel lipped trays per door, gliding type
- Double pane hinged glass door with door lock
- Vibration dampening at all metal to metal contact points
- Padded feet (one inch high) to isolate chamber from floor vibrations
- Electric condensate evaporator
- Removable instrument panel reduces height by 4" to facilitate moving through doorways
- Pre-charged condensing unit for mounting on wall next to chamber
- One year parts and labor warranty
- Four additional years on compressor (part only)



Model
PCT33SD



Model
PCT70SD

Model	Style	Temp. Range and Uniformity	Capacity (ft ³ /liters)	Total Shelf Area (ft ² /m ²)	Dimensions		Electrical (domestic)	HP	Shipping Weight (lbs/kg)
					Exterior* (in/cm)	Interior (in/cm)			
PCT33SD		5-30°C $\pm 1^{\circ}\text{C}$	31/880	37.5/3.5	33/84	W 29/74	115/60/1 20 amps 5-20 plug	1/3	650/295
					29/74	D 25/64			
					78.5/199	H 69/175			
PCT70SD		5-40°C $\pm 1^{\circ}\text{C}$	72/2040	75/7	70/178	W 66/167	115/60/1 30 amps L530 plug	1/2	950/432
					31/79	D 26/66			
					78.5/199	H 69/175			

*Padded feet add an additional 1" to the exterior height after installation.



BETATEK INC.

Instrumentation Superbly Supported

L'instrumentation à son meilleur

654 Petrolia Road,
Toronto, ON M3J 2W3
Tel: (416) 736-6166
Toll-Free: (800) 387 3570
Fax: (416) 736-9346