







Temperature Only or Temperature/Humidity Stability Chambers

Designed to provide controlled temperature or temperature/humidity environments for shelf life testing of cosmeceutical, nutraceutical and pharmaceutical products and packaging, these chambers offer FDA and ICH compliance at a reasonable price. Each chamber has an alarm to monitor chamber performance with an access port for remote sensors to record data (optional chart recorder). Conditioned air flows horizontally through louvered portholes that balance air pressure for even distribution across each tray. Ten levels of stainless steel lipped trays offer 37.5 or 72 ft² (3.5 or 7 m²) of storage space, depending on the model. The stainless steel cabinet has heated double-glass doors (optional solid) for quick product identification to minimize door-ajar disruptions. Both the chamber door(s) and control panel are lockable. Options available include RS-232 ports or retransmit outputs for remote monitoring and ultra-pure DI water re-circulation systems for applications where high quality water is not available.

- ~ Microprocessor controlled temperature range, ± 0.5°C at the sensor
- ~ Microprocessor controlled additive RH, 50-80% RH, ± 2% at the sensor (if ordered)
- ~ Audible/visual hi-low alarm (temperature only or temperature/RH, depending on chamber ordered)
- ~ Access port for remote sensor entry
- ~ OPTIONAL chart recorder, seven day (1 pen or 2 pens, depending on need)
- ~ Lockable Plexiglas control panel cover
- ~ High and low temperature failsafes
- ~ Stainless steel interior and exterior
- ~ Ten stainless steel trays per door
- ~ Lockable, double pane hinged and heated glass doors
- ~ Locking casters, 4"
- ~ Condensate pump (for temperature/RH chambers)
- ~ Height of chamber sized to fit through 32" x 78" doorways
- ~ One year parts and labor warranty
- ~ Four additional years on the compressor (part only)

| Model | Style | Temp Selection and Uniformity | Humidity Selection and Uniformity | Capacity (ft ³ /liters) | Total Shelf Area (ft ² /m ²) | Dimensions | | | Electrical Required (Domestic) | HP | Shipping Weight (lbs/kg) |
|------------|---|-------------------------------|-----------------------------------|------------------------------------|---|-----------------------------------|---------------------------|-------------------------|--------------------------------|----------|--------------------------|
| | | | | | | Exterior** (in/cm) | Interior (in/cm) | Interior (in/cm) | | | |
| SLT52SD/T |  | 5-20°C ±0.5°C* | None | 31/880 | 37.5/3.5 | 52/132 W 29/74 D 74.5/189 H | 29/74 25/64 69/175 | 115/60/1 L5-20P | 1/3 | 700/320 | |
| SLT52SD/T |  | 20-50°C ±0.5°C* | None | 31/880 | 37.5/3.5 | 52/132 W 29/74 D 74.5/189 H | 29/74 25/64 69/175 | 115/60/1 L5-20P | 1/3 | 700/320 | |
| SLT52SD/RH |  | 20-50°C ±0.5°C* | 50-80% ±2%* | 31/880 | 37.5/3.5 | 52/132 W 29/74 D 74.5/189 H | 29/74 25/64 69/175 | 115/60/1 L5-30P | 1/3 | 700/320 | |
| SLT89SD/T |  | 5-20°C ±0.5°C* | None | 72/2040 | 75/7 | 89/226 W 31/79 D 77/196 H | 66/167 26/66 69/175 | 115/60/1 L5-30P | 1/2 | 1000/455 | |
| SLT89SD/T |  | 20-50°C ±0.5°C* | None | 72/2040 | 75/7 | 89/226 W 31/79 D 77/196 H | 66/167 26/66 69/175 | 115/60/1 L5-30P | 1/2 | 1000/455 | |
| SLT89SD/RH |  | 20-50°C ±0.5°C* | 50-80% ±2%* | 72/2040 | 75/7 | 89/226 W 31/79 D 77/196 H | 66/167 26/66 69/175 | 115/230/60/1 L14-30P | 1/2 | 1000/455 | |

Temp/RH chambers are designed for one combination of parameters unless specified at time of order.
 *At the sensor **Exterior height before casters are installed



Model SLT89SD/RH with optional chart recorder

Ultra pure Water Recirculation System (optional)

Model SLT52SD/RH with optional chart recorder



BETATEK INC.

Instrumentation Superbly Supported

L'instrumentation à son meilleur

654 Petrolia Road,
Toronto, ON M3J 2W3
Tel: (416) 736-6166
Toll-Free: (800) 387 3570
Fax: (416) 736-9346